

Trinkwasseranlagen/Watermaker

Von 15 - 200 lt./h

SIGNALLING DEVICES & FIRST AID

SOUND SIGNAL	MEANING	ADVISOR
•	Altering course to STARBOARD.	
••	Altering course to PORT.	
•••	Going Astern.	
••••	Identity signal of a Pilot vessel.	
••••• (at least 5)	Uncertainty, for danger of collision with other boat.	
IIII	Boat approaching the turning point of channel or river.	
IIII	Response signal from a boat approaching the opposite direction of the channel's or river's turning point.	
IIII	Power boat.	
IIII IIII	Power boat at sea, but standing by.	
IIII ••	Boat not under command, boat with limited maneuverability, either anchored or not, boat restricted by its draught, boat under sail, anchored fishing boat, boat that tows or propels another boat.	
IIII •••	Towed boat (or the last manned towed boat, in case there are more than one).	
IIII IIII •	Intentions of passing from the starboard side of your boat (***)	
IIII IIII ••	Intentions of passing from the port side of your boat (***)	
IIII • IIII •	Response signal from a boat to be passed, provided that agrees with the passing movement. (***)	
••• IIII •••	SOS signal using sound or visual communication devices.	

(***) : They apply to narrow channels or rivers.
• : Short blast (about 1sec of duration).
IIII : Longe blast (about 4-6sec of duration).

BEST
VALUE

NEW

Signalling Mirror 7x7cm

C* 236731 2,70 €


INSTRUCTIONS OF USE

1. Hold foresight in left hand with arm fully extended.
2. Hold the signalling mirror in right hand toward the sunlight, facing the back of the mirror.
3. Align the holes of the foresight and the mirror on the target.
4. Move mirror until the reflection of the sun from the mirror can be seen on the foresight, and a shadow point appears in its hole.
5. The ray is now directed at the target.



First Aid Box

Specifically designed for use on boats.
Made from durable ABS plastic.
Compact, solid, watertight. Screw down plastic base plate for quick release.
Dimensions: 21x21x12,5cm



All first aid boxes are supplied empty.

First Aid Box
(Base is not included)
C* auf Anfrage

Base for First Aid Box
C* 125465 2,63 €



Fog Horn Head Only
C* 102293 4,11 €

Complete Units in Blister Packing

Signal Horn 380ml Acoustic range approximately 1500 m.



Refill Horn Canister
C* 102290 4,11 €



SignalHorn & Refilling
Canister in Blister Pack
B* 102286 8,09 €



1. Install horn by screwing it on the pressurized container.



2. To operate press down the horn.



3. Signal horn must always be used in upright position.



4. Do not store the pressurized container in direct sunlight. Do not expose to temperatures exceeding 40°C. Do not pierce or burn, even after use.

BEST
VALUE

NEW

Signal Horn
Set 'Echo-200'
- 200ml

C* 236782 5,97 €

BEST
VALUE

NEW

Signal Horn
Set 'Echo-380'
- 380ml

C* 236807 7,35 €

BEST
VALUE

NEW

Refill Canister 200ml for
Signal Horn 'Echo-200'
C* 236741 3,24 €

BEST
VALUE

NEW

Refill Canister 380ml for
Signal Horn 'Echo-380'
C* 236750 3,45 €

BEST
VALUE

NEW

Fog Horn Head Only for
'Echo-200' & 'Echo-380'
C* 236757 3,90 €



Mega Horn

Whether you use Mega Horn in an emergency or for pleasure you certainly will be heard. Sound measures at 105 D.B. Available in red colour, it comes complete with counter merchandising display box. Floating, non corrosive. Friendly to the environment.
Available in showcases of 12pcs.

C* 103109 6,15 €